


SUPACARB

AMAZON

DUAL FUNCTION DEPTH CARTRIDGE



SUPACARB filter cartridges feature a choice of rolled felt carbon impregnated media or a superior sintered carbon block, both combined with Amazon Filters unique spun bonded particulate removal layers resulting in a genuine dual purpose element.

The **SUPACARB RP/XP** series offer economy with efficiency for chlorine, odour, colour and trace organic reduction levels, whilst the **SUPACARB BP** use a unique sintered carbon technology that combines the best features of both powdered (PAC) and granular (GAC) activated carbon in one cartridge. Both element styles use the SupaGard spun bonded media for the pre-filtration layer and are available with moulded polymer ends for superior sealing and enhanced product performance.

SUPACARB offers an extremely economical solution to many common liquid treatment applications.

Product Features - RP/XP

- Multiple layered carbon impregnated polyester felt
- One piece construction up to 1015mm (40")
- Polymer materials meet US FDA Title 21 requirements

The construction of **SUPACARB RP/XP** uses a polyester substrate, unlike many other rolled elements that use a cellulose based support. This minimises the risk of microbiological contamination and allows its use in a wider range of chemical applications because of its better compatibility.

Product Features - BP

- Unique sintered block using both granular and powdered carbon
- Modular construction up to 1017mm (40")
- Polymer materials meet US FDA Title 21 requirements

The modular **SUPACARB BP** uses a unique sintering process that combines high purity powdered and granular carbon, this results in the very highest available surface area for a 10" cartridge. Superior adsorption and on-stream life makes the **BP** the very best choice of carbon cartridges.

Equipped with 5µm nominal rated spun bonded polypropylene pre-filtration layers and a full range of welded end caps, it makes the **SUPACARB** the ideal choice of activated carbon cartridges. Compared with conventional Granular Activated Carbon cartridges, the **SUPACARB** will not fluidise, channel or bypass, therefore maximising the effectiveness of the carbon media.



SUPACARB FEATURES AND BENEFITS

- Large carbon surface area exhibits excellent chlorine reduction characteristics
- Graded density pre-filtration layer for effective sediment removal and protection of the carbon media
- All polymeric construction offers excellent chemical compatibility and stability in aqueous solutions
- Minimal carbon release when compared to conventional loose filled granular (GAC) style cartridges
- Identification embossed on every cartridge
- Construction eliminates fluidising, channelling or bypass
- Can be sanitised and steam sterilised

See product guides for further details of test methods and rated efficiencies

SUPACARB

TECHNICAL DATA

Dimensions

Outside Diameter: 66.5mm
 Core Diameter: 27mm
 Length: See ordering guide

Sterilisation and Sanitisation*1

Steam: 121°C for 15 mins (20 cycles)
 Hot Water: 90°C for 30 mins (0.2 bar Δp max)

*1Applies to single open end cartridges only. For all steaming and hot water applications, the Glass Filled end cap option must be used

Maximum Operating Conditions

Temperature: 80°C
 Recommended Maximum Differential Pressure: 1.5 Bar

Product validation guide available on request. All SUPACARB cartridges are manufactured under strict control with batch number identification, giving full traceability on all components.

Chlorine Reduction Capacity Data

Cartridge Type	Flow Rate (litres/min)	Chlorine reduction capacity (litres)
06RP	3.7	>2000
06XP	3.7	>10000
06BP	3.7	>75000

The above test is based on challenging a 10" filter with water containing 3.0 ppm of free chlorine. The chlorine reduction capacity is the volume, in litres, of water from which the filter will successfully remove >96% of free chlorine present upstream of the filter when operating at given flow rate.

Flow Rate

Cartridge Type	Max. flow rate for odour, taste and chlorine reduction (litres/min)	Recommended max. flow rate for >96% chlorine reduction capacity (litres/min)
06RP	8 @ 20mBarΔp	3.7 @ 10mBarΔp
06XP	15 @ 40mBarΔp	3.7 @ 10mBarΔp
06BP	15 @ 280mBarΔp	3.7 @ 70mBarΔp

Note: For safety reasons, the Amazon SupaCarb range of cartridge elements should only be used on microbiologically safe water supplies. Activated carbon cartridges are not designed to remove or kill bacteria or viruses. All the data shown should be treated with caution, actual results will vary with the different combinations of organic content present, pH variations and temperature, and should not be considered a warranty of any kind.

ORDERING GUIDE

CARBON/MEDIA	MICRON RATING	LENGTH	CONNECTIONS	SEAL	OPTIONS
BP - Sintered Block RP - Rolled Felt XP - High Volume Rolled Felt RD - Rolled Felt, Glass Filled PP core XD - High Volume Rolled Felt, Glass Filled PP core	005 - 5.0µm	RP/XP 09 - 252mm 20 - 507 26 - 663 30 - 760 40 - 1015 BP 09 - 249mm 20 - 509 30 - 763 40 - 1017	N - None (RP/XP Only) 0 - DOE (BP) A - Code A B - Code B*2 S - Code S 2 - Code 2 3 - Code 3 7 - Code 7 8 - Code 8	P - PE Gasket (RP/XP, DOE Only) B - Buna E - EPDM F - FEP/Silicone (SOE Only) S - Silicone V - Viton	G - Glass filled end cap

Example: 06RP005-203EA = Rolled Felt media, 5.0µm rating, double length 20" long, code 3 connections with EPDM seal.

*2 Code B - to fit Amazon 50 series housings only.

INDUSTRIES AND APPLICATIONS

- | | |
|--|--|
| Metal Finishing
Fine Chemicals
Food and Beverage
Water Treatment
Pharmaceutical | <ul style="list-style-type: none"> • Organic reduction in plating baths • Colour reduction in solvents • Colour reduction in alcohol, Bottled waters, General clarification, Ozone reduction • Small scale chlorine, odour, colour and trace organic reduction • Colour reduction in solvents |
|--|--|

AMAZON FILTERS LTD.

ALBANY PARK ESTATE, FRIMLEY ROAD,
 CAMBERLEY, SURREY, GU16 7PG
 ENGLAND

Tel: +44 (0) 1276 670 600
 Fax: +44 (0) 1276 670 101
 Email: sales@amazonfilters.co.uk
 Web: www.amazonfilters.co.uk



Certificate No. FM39584

Distributed by: